

PRODUCT DATASHEET

1906 BUBBLE PENDANT 200x1215 Glass Smoke

Vintage 1906 Bubble | Indoor glass luminaires, vintage style, E27 socket, round shaped lamp shade



AREAS OF APPLICATION

- Living areas (living rooms, dining rooms, bedrooms etc.)
- Bars, restaurants

PRODUCT BENEFITS

- Adjustable appearance thanks to use of separate available E27 lamp shapes
- Easy and quick installation

PRODUCT FEATURES

- Glass luminaires with a round shaped lamp shade
- Special vintage appearance when combined with 1906 LED or halogen lamps
- Luminaire family for various application areas
- Available in various colors




TECHNICAL DATA

Electrical data

Operating mode	Mains voltage
Nominal voltage	220...240 V
Mains frequency	50/60 Hz

Dimensions & weight



Width	100.0 mm
Diameter	200.0 mm
Height	1460 mm
Product weight	800.00 g

Colors & materials

Body material	Glass
Housing color	Smoke-grey
Product color	Smoke-grey
Cover material	Glass

Temperatures & operating conditions

Ambient temperature range	-20...40 °C
----------------------------------	-------------

Additional product data

Product remark	Available from April 2019
-----------------------	---------------------------

Capabilities

Dimmable	No
Type of connection	Terminal
Holder designation	E27

Certificates & standards

Protection class	I
Type of protection	IP20
Standards	CEEACREACH

EQUIPMENT / ACCESSORIES

- No light sources included
- Complete mounting and connecting accessories included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075217409	Folding carton box 1	263 mm x 263 mm x 368 mm	1096.00 g	25.45 dm ³
4058075217416	Shipping carton box 6	800 mm x 540 mm x 380 mm	8133.00 g	164.16 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.