



Cable Cover, Material: PA6, UL94V0

Helawrap HWPV0

Helawrap HWPV0 is used to bundle and protect cable and wires, especially there is vibration and abrasion. HWPV0 has excellent flame-retardant properties and is halogen-free.

Features and Benefits

- Ideal solution for bundling, protecting and fixing cables
- Quick and effortless to apply
- Self-extinguishing according to UL94 V0
- Very good abrasion protection
- Special profile enables branching off cable at any point
- Can be removed and reapplied often
- Available in several colours and sizes
- Handy applicator tool included



Cables can be branched off at any point for better, more flexible protection.

MATERIAL	Polyamide 6 V0 (PA6V0)
Operating Temperature	-40 °C to +90 °C, intermittent +120 °C
Flammability	UL94 V0
Specifications	CEN TS 45545-2: 2009, DIN 5510-2, UL-Recognised



TYPE	Bundle Ø max.	Colour	Reel Length	Application Tool	Article-No.
HWPV08	9.1	Black (BK)	25 m	HAT8	161-63101
HWPV016	16.0	Black (BK)	25 m	HAT16	161-63201
HWPV020	21.1	Black (BK)	25 m	HAT20	161-63301
HWPV025	26.9	Black (BK)	25 m	HAT25	161-63401
HWPV030	32.0	Black (BK)	25 m	HAT30	161-63501

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.