

**Technical Data**

|          |                                                          |
|----------|----------------------------------------------------------|
| Material | : Ethylene Propylene Rubber<br>Isobutene-Isoprene-Rubber |
| Colour   | : black                                                  |

| Specification         | Typical Value               | Test Method |
|-----------------------|-----------------------------|-------------|
| Thickness             | : 1.65 mm                   | ASTM-D-4325 |
| Operating Temperature |                             |             |
| Continues             | : up to +80 °C              | ASTM-D-4388 |
| Short Term            | : up to +130 °C             | ASTM-D-4388 |
| Water Absorption      | : 0.10 %                    | ASTM-D-570  |
| Volume Resistivity    | : $10^{13} \Omega\text{cm}$ | ASTM-D-4325 |
| Dielectric Strength   | : 400 V/mm                  | ASTM-D-4325 |
| UV Resistance         | : pass                      | ASTM-D-4325 |
| Ozone Resistance      | : pass                      | ASTM-D-4325 |