


Data Sheet

25 pcs RGB LED with 300mm Cable, 12V/DC




Ø3mm RGB LED Cable Set



B/N	Item no.	Light Source	RGB		
2102589	T1810O093	Wavelength / color temperature	R:620-625	G:520-525	B:465-470
		Max. Luminous intensity	R:1000-1500	G:4000-5000	B:2000-3000
		Viewing angle (typ.)	30°		
		Forward current (max.)	20mA		
		Forward voltage (typ.)	12V		
		Contents	25 pcs		

Ø5mm RGB LED Cable Set



B/N	Item no.	Light Source	RGB		
2102610	T1810O113	Wavelength / color temperature	R:620-625	G:520-525	B:465-470
		Max. Luminous intensity	R:1800-2500	G:5000-6000	B:3000-4000
		Viewing angle (typ.)	30°		
		Forward current (max.)	20mA		
		Forward voltage (typ.)	12V		
		Contents	25 pcs		