

Data Sheet

300mm LED Cable assortment



T1810094

Ø3mm Mixed color LED Cable Set



Light Source	Red	Blue	Green	Yellow	White
Wavelength / color temperature	625-635nm	460-465nm	568-572nm	587-590nm	3000-3200K
Max. Luminous intensity	600mcd	1500mcd	100mcd	600mcd	9000mcd
Viewing angle (typ.)	30°	30°	30°	30°	25°
Forward current (max.)	20mA	20mA	20mA	20mA	20mA
Forward voltage (typ.)	12V	12V	12V	12V	12V

T18100114

Ø5mm Mixed color LED Cable Set



Light Source	Red	Blue	Green	Yellow	White
Wavelength / color temperature	620-625nm	460-470nm	568-572nm	587-590nm	3000-3200K
Max. Luminous intensity	800mcd	2000mcd	120mcd	800mcd	20000mcd
Viewing angle (typ.)	35°	35°	35°	35°	25°
Forward current (max.)	20mA	30mA	20mA	30mA	20mA
Forward voltage (typ.)	12V	12V	12V	12V	12V