

Data Sheet

300mm LED Cable assortment



Ø3mm LED Cable Set



Item number	T1810O095	T1810O096	T1810O097	T1810O098	T1810O099	T1810O100	T1810O101	T1810O102
Light Source	Red	Blue	Green	Yellow	White	White	White	White
Wavelength / color temperature	625-635nm	460-465nm	568-572nm	587-590nm	2700-3000K	3000-3200K	4000-4500K	6000-6500K
Max. Luminous intensity	600mcd	1500mcd	100mcd	600mcd	9000mcd	9000mcd	9000mcd	8000mcd
Viewing angle (typ.)	30°	30°	30°	30°	25°	25°	25°	30°
Forward current (max.)	20mA	20mA	20mA	20mA	20mA	20mA	20mA	20mA
Forward voltage (typ.)	24V	24V	24V	24V	24V	24V	24V	24V

Ø5mm LED Cable Set



Item number	T1810O115	T1810O116	T1810O117	T1810O118	T1810O119	T1810O120	T1810O121	T1810O122
Light Source	Red	Blue	Green	Yellow	White	White	White	White
Wavelength / color temperature	620-625nm	460-470nm	568-572nm	587-590nm	2700-3000K	3000-3200K	4000-4500K	6000-6500K
Max. Luminous intensity	800mcd	2000mcd	120mcd	800mcd	20000mcd	20000mcd	14000mcd	14000mcd
Viewing angle (typ.)	35°	35°	35°	35°	25°	25°	25°	20°
Forward current (max.)	20mA	30mA	20mA	30mA	20mA	20mA	20mA	20mA
Forward voltage (typ.)	24V	24V	24V	24V	24V	24V	24V	24V