

# KERN CT3000-3Q1

Scherstab-Messzellen aus rostfreiem Stahl mit IP69-Schutz



## Measuring system

Combined Error:	0,017 %
Load cell connection:	6-Leiter
Nominal sensitivity:	2
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	3 t
Y value:	10000

## Environmental conditions

Maximum operating temperature:	70 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-30 °C
Minimum operating temperature:	-10 °C

## Category

Brand:	Sauter
--------	--------

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	285 x 115 x 85 mm
Gross weight:	2,334 kg
Net weight:	2,200 kg
Shipping method:	Parcel service

## Construction

Cable length:	5 m
Dimensions (WxDxH):	171,5 x 48 x 41,5 mm

## Piktogramme

### STANDARD

