

KERN CR 2500-1Q1

Load cells made of stainless steel



Measuring system

Combined Error:	0,050 %
Load cell connection:	4-Leiter
Nominal sensitivity:	2
OIML class:	C1
Resolution Load cell â Verifiable:	1000e
Weighing capacity [Max]:	2,500 t
Y value:	10000

Environmental conditions

Maximum operating temperature:	70 °C
Maximum operate temperature:	40 °C
Minimum ambient temperature:	-50 °C
Minimum operating temperature:	-10 °C

Category

Brand:	Sauter
--------	--------

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	250 x 155 x 60 mm
Gross weight:	1,096 kg
Net weight:	1,050 kg
Shipping method:	Parcel service

Construction

Cable length:	10 m
---------------	------

Piktogramme

STANDARD

