

KERN CP400-3P2

Aluminium singlepoint load cell



Measuring system

Combined Error:	0,023 %
Load cell connection:	4-Leiter
Nominal sensitivity:	2
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	400 kg
Y value:	10000

Environmental conditions

Maximum operating temperature:	65 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-35 °C
Minimum operating temperature:	-10 °C

Category

Brand:	Sauter
--------	--------

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	160 x 105 x 110 mm
Gross weight:	760 g
Net weight:	706 g
Shipping method:	Parcel service

Construction

Cable length:	2 m
Dimensions (WxDxH):	150 x 44 x 40 mm
Dimensions of weighing plate (WxDxH):	450 x 450 x 0 mm