

# KERN CB 10-3Q1

Biegestabwägezellen aus rostfreiem Stahl



## Measuring system

Combined Error:	0,017 %
Load cell connection:	4-Leiter
Nominal sensitivity:	2
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	10 kg
Y value:	10000

## Environmental conditions

Maximum operating temperature:	70 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-30 °C
Minimum operating temperature:	-10 °C

## Category

Brand:	Sauter
--------	--------

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	250 x 155 x 60 mm
Gross weight:	532 g
Net weight:	500 g
Shipping method:	Parcel service

## Construction

Cable length:	3 m
---------------	-----

## Piktogramme

STANDARD

