

KERN CP50-3P3

Single-point load cells made of anodised aluminium



Measuring system

| | |
|------------------------------------|----------|
| Combined Error: | 0,023 % |
| Load cell connection: | 6-Leiter |
| Nominal sensitivity: | 2 |
| OIML class: | C3 |
| Resolution Load cell â Verifiable: | 3000 e |
| Weighing capacity [Max]: | 50 kg |
| Y value: | 10000 |

Environmental conditions

| | |
|--------------------------------|--------|
| Maximum operating temperature: | 65 °C |
| Maximum operating temperature: | 40 °C |
| Minimum ambient temperature: | -35 °C |
| Minimum operating temperature: | -10 °C |

Category

| | |
|--------|--------|
| Brand: | Sauter |
|--------|--------|

Packaging & shipping

| | |
|-------------------------------|-------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 225 x 115 x 35 mm |
| Gross weight: | 439 g |
| Net weight: | 389 g |
| Shipping method: | Parcel service |

Construction

| | |
|---------------------------------------|--------------------|
| Cable length: | 3 m |
| Dimensions (WxDxH): | 150 x 25,4 x 40 mm |
| Dimensions of weighing plate (WxDxH): | 350 x 400 x 0 mm |