

KERN CP75-3P3

Single-point load cells made of anodised aluminium



Measuring system

Combined Error:	0,023 %
Load cell connection:	6-Leiter
Nominal sensitivity:	2
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	75 kg
Y value:	12000

Environmental conditions

Maximum operating temperature:	65 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-35 °C
Minimum operating temperature:	-10 °C

Category

Brand:	Sauter
--------	--------

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	225 x 115 x 35 mm
Gross weight:	439 g
Net weight:	389 g
Shipping method:	Parcel service

Construction

Cable length:	3 m
Dimensions (WxDxH):	150 x 25,4 x 40 mm
Dimensions of weighing plate (WxDxH):	350 x 400 x 0 mm