

# KERN CR 20000-1Q1

Load cells made of stainless steel



## Measuring system

Combined Error:	0,050 %
Load cell connection:	4-Leiter
Nominal sensitivity:	2
OIML class:	C1
Resolution Load cell â Verifiable:	1000e
Weighing capacity [Max]:	20 t
Y value:	10000

## Environmental conditions

Maximum operating temperature:	70 °C
Maximum operate:	40 °C
Minimum ambient temperature:	-50 °C
Minimum operating temperature:	-10 °C

## Category

Brand:	Sauter
--------	--------

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	220 x 135 x 100 mm
Gross weight:	2,919 kg
Net weight:	2,800 kg
Shipping method:	Parcel service

## Construction

Cable length:	10 m
---------------	------

## Piktogramme

STANDARD

