

KERN CR 30000-1Q1

Load cells made of stainless steel



Measuring system

| | |
|------------------------------------|----------|
| Combined Error: | 0,050 % |
| Load cell connection: | 4-Leiter |
| Nominal sensitivity: | 2 |
| OIML class: | C1 |
| Resolution Load cell â Verifiable: | 1000e |
| Weighing capacity [Max]: | 30 t |
| Y value: | 10000 |

Environmental conditions

| | |
|--------------------------------|--------|
| Maximum operating temperature: | 70 °C |
| Maximum operating temperature: | 40 °C |
| Minimum ambient temperature: | -50 °C |
| Minimum operating temperature: | -10 °C |

Category

| | |
|--------|--------|
| Brand: | Sauter |
|--------|--------|

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 220 x 135 x 100 mm |
| Gross weight: | 3,070 kg |
| Net weight: | 2,800 kg |
| Shipping method: | Parcel service |

Construction

| | |
|---------------|------|
| Cable length: | 10 m |
|---------------|------|

Piktogramme

STANDARD

