

VIEW3 LITE



13 MP
DUAL CAM

Dual camera with bokeh mode



32 GB
ROM

Large storage



1.6 GHz
OCTACORE

Powerful performance



4000 MAH

Full day autonomy



Big memory. Big battery.

Discover a complete smartphone experience within everyone's reach :

- dual camera
- large memory
- big battery

Available colors: ● Night blue ● Blush Gold ● Arctic bleen

CUSTOMISED ACCESSORIES

- **Smart Folio** with standing option to enjoy your contents hands-free
- Slim **Clear Case** with hard back cover and flexible frame
- Ultra-resistant **Printed Tempered Glass** that prevent your phone against scratches

Main features	
Network	4G LTE B1 (2100)/ B3 (1800)/ B5 (850) / B7 (2600)/ B8 (900) / B20 (800) / B28B(700) / B40 (2300) H+/3G+/3G HSPA+ 850/ 900/ 1900/ 2100 MHz GSM/GPRS/EDGE 850/900/1800/1900 MHz
Data Segment	FDD-LTE Category 4 DL 150 Mbps, UL 50 Mbps
Operating System	Android™ 9 Pie
Processor	Unisoc SC9863A, Octa-Core 1.6GHz
GPU	IMG 8322
Design	Touch screen
SIM CARD	2 Nano SIM
Available colors	Night Blue, Blush Gold, Arctic Bleen
Size	155.5 x 73 x 8.7mm
Weight	160.1g
Battery	4000 mAh Li-Po
Stand-by time	Up to 265h
Talk time	Up to 30h (2G), 25h (3G)
ROM	32 GB
RAM	2 GB
External memory	Micro SD up to 128 GB
Accelerometer	Yes
Magnetic sensor	Yes
Proximity sensor	Yes
Light sensor	Yes
SAR value	Head: 0.533 W/Kg, Body: 1.326 W/kg
Display	
Size	6.09
Type	IPS Technology, Full Lamination, 2.5D
Color	16 million
Display resolution	HD+ (1560 x 720 pixels), pixel density: 282ppi
Multitouch	Yes
Connectivity	
Wi-Fi	802.11 b/g/n
Tethering	USB, Bluetooth, Access Point Wi-Fi
Bluetooth®	4.2
USB™ OTG	Yes
PORT USB™	2.0
PC synchronization	Yes
Audio jack	3.5mm jack
Photo & Video	
Main camera	Dual 13 MP (Main) + 2 MP (Depth)
Option	Face Beauty, Night Mode, HDR, Live Filter, Time-Lapse, Live Portrait (front), Live Artistic Blur (rear), AI mode, Professional mode
Flash	LED
Front Camera	5 Megapixels

Digital Zoom	4x
Auto Focus	Yes
Image editor	Yes
White Balance	Auto, Incandescent, Daylight, Fluorescent, Cloudy
Video recorder	1080p@30fps

Multimedia and Entertainment	
Supported sound formats	MP3, MIDI, AAC, AMR
Supported image formats	JPEG, GIF, PNG, BMP
Supported video formats	3GPP, MP4, 3GP, H.264

GPS system	
GPS	Yes
A-GPS	Yes

Customization	
Languages	English, French, Italian, German, Dutch, Spanish, Portuguese, Russian, Czech, Polish, Finnish, Hungarian, Arabic, Urdu, Persian, Danish, Norwegian, Swedish, Thai, Indonesian, Vietnamese, Turkish, Cyrillic Serbian, Latin Serbian, Slovenian, Macedonian, Croatian, Catalan, Basque, Romanian, Polish, Slovak, Ukrainian, Greek
Wiko features	Face Unlock, Wiko Launcher, One Handed Mode, Simple Mode, Smart Assist, Smart Action

Google™ Mobile Service	
Applications	Yes

In the box	
	AC adapter Headset Micro USB Cable Wiko mobile phone Quick Start Guide Safety Book

Specifications, features and appearance of the product may be altered without notification. Access to Google™ applications can differ depending on your country.

