

# JT-AT34

Low Cost USB 3.0 Volt-/ Amperemeter



The AT-34 is a small but multifunctional USB multimeter. By supporting current Quick Charge standards, it can also be easily used in conjunction with current handheld hardware.

## MAIN FEATURES

Screen	0,96 Zoll IPS Display
Refresh rate	2 Hz
Interface	USB 3.0 (2.0 compatible)
Quick Charge Recognition	QC2.0, QC3.0, Apple 2.4A /2.1A/1A/0.5A, Android DCP, Samsung
Size	64 x 22 x 12 mm
Items delivered	JT-AT34 USB meter

## FURTHER SPECIFICATIONS

Voltage measurement range	3,7 - 30 V
Voltage resolution	0,01 V
Voltage accuracy	±0,8 %(+4 digits)
Current measurem. Range	0 - 4 A
Current resolution	0,001 A
Current accuracy	±1 %(+4 digits)
Power measurement range	0 - 120 W
Capacity accumul. range	0 - 99999 mAh
Energy accumulation range	0-99'999mWh (999,99Wh)
Load impedance range	1 – 9'999.9 Ω
Temp. measurement range	0 °C - 80 °C
Work temperature range	0 – 45 °C
Temp. measurement error	± 3 °C

## FURTHER DETAILS

Article number	JT-AT34
EAN	4250236818696
Costums Tariff No.	8473302000