

JT-T66C

USB type C 3.0 Volt-/ Amperemeter



The TC66C is a small but multifunctional USB C multimeter. Due to the support of current Quick Charge Standards it can also be used in conjunction with current handheld hardware.

MAIN FEATURES

Screen	0,96 Zoll IPS Display
Refresh rate	2 Hz
Interface	USB type C
Quick Charge Recognition	QC2.0, QC3.0, Huawei FCP, Huawei SCP, SAMSUNG AFC,
Size	49 x 22 x 8 mm
Items delivered	JT-TC66C USB meter

FURTHER SPECIFICATIONS

Voltage input	3,5—24 V
Voltage measurement range	0,005 - 30 V
Voltage resolution	0,1 mV
Voltage accuracy	± 0,5 ‰ (+10 digits)
Current measurement. Range	0 - 5 A
Current resolution	0,01 mA
Current accuracy	± 1 ‰ (+20 digits)
Power measurement range	0 - 150 W
Capacity accumul. range	0 - 99999 mAh
Energy accumulation range	0-99'999mWh (999,99Wh)
Load impedance range	1 - 9'999.9 Ω
Temp. measurement range	0 °C - 80 °C
Work temperature range	0 - 45 °C

FURTHER DETAILS

Article number	JT-TC66C
EAN	4250236818689
Costums Tariff No.	8473302000