

KERN TGD50-3CS05

Compact pocket carat balance for precision weighing of jewellery and precious stones



Measuring system

Adjustment options:	External calibration
Linearity:	3 mg
Readability [d]:	1 mg
Recommended adjusting weight:	50 g (F2)
Repeatability:	3 mg
Resolution:	50000
Stabilisation time under laboratory conditions:	3 s
Tare range:	50 g
Warm up time:	2 h
Weighing capacity [Max]:	50 g
Weighing system:	Strain gauge
Weighing units:	ct dwt g gn oz ozt

Display

Display digit height:	2 cm
-----------------------	------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C
Minimum humidity:	15 %

Power supply

Battery:	4x1.5 V AAA
Operating time:	150 h

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand:	KERN
Category:	Balances
Product Group:	Pocket balance

Packaging & shipping

Delivery:	24 h
Gross weight:	2,215 kg
Net weight:	980 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	96 x 149 x 36 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (d):	65

Piktogramme

STANDARD



OPTION

