



Slim pocket balance with large stainless steel weighing plate and practical tare pan

Features

- High-resolution pocket balance with particularly rapid reaction and stabilisation time, which means that you can work extremely efficiently
- Particularly flat design
- **1** Cover made of shock proof plastic as protection against pressure and dust. Can also be used as a tare cup
- Stainless steel weighing plate, which makes cleaning easy and hygienic
- Ready for use: Batteries included, 2×CR2032, operating time up to 8,75 h. Integrated AUTO-OFF function after 4 minutes to preserve the batteries



Compact pocket carat balance for precision weighing of jewellery and precious stones

Features

- Simple and convenient 4-key operation
- Can be switched over from g to ct, gn, dwt, ozt, oz at the touch of a key
- Large touch-sensitive, backlit touch display with very good contrast for easy operation and convenient reading
- Hard case cover as protection against pressure and dust
- Stainless steel weighing plate, which makes cleaning easy and hygienic
- Weighing pan standard
- Powder scale with Grain division (gn), ideal for sport shooters, reloaders etc. for self-filling cartridge cases
- USB cable for power supply as standard
- Ready for use: Batteries included, 4×1.5 V AAA, operating time up to 150 h. Integrated AUTO-OFF function after 5 minutes to preserve the batteries
- **2** Delivered in single design packaging

Discover more details and matching accessories online!



STANDARD



1 DAY

OPTION



DAkks



STANDARD



1 DAY

OPTION



DAkks

KERN Model	TGC 150-2	TGC 500-1	TGC 1K-3	TGD 50-3C
Weighing capacity [Max] g	150	500	1000	50
Readability [d] g	0,01	0,1	1	0,001
LCD display – backlit		yes		yes
LCD display – digit height		12 mm		20 mm
Dimensions of weighing surface W×D		81 mm		65 mm
Overall dimensions W×D×H		100×130×18 mm		96×150×64 mm
Net weight	200 g	150 g	150 g	250 g
Permissible ambient temperature		0 °C – 40 °C		5 °C – 35 °C
Option Calibr. Certificate DAkks accr.		963-127		963-127