

KERN MGD200K-1LS05



Elegant look combined with large, flat glass weighing plate to make it easier to step on and give maximum safety



Construction

Dimensions of weighing plate (WxDxH):	380 x 330 x 27 mm
Overall dimensions mounted (WxDxH):	380 x 330 x 27 mm
Weighing surface (WxD):	380 x 330 mm

Piktogramme

STANDARD



Measuring system

Adjustment options:	Calibration not possible
Linearity:	1,350 kg
Precision (of [Max]):	0,500 %
Readability [d]:	100 g
Repeatability:	1,350 kg
Resolution:	2500
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	250 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	5 cm
-----------------------	------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	5 %

Power supply

Operating time:	100 h
-----------------	-------

Category

Brand:	KERN
Product Group:	Personal floor scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	410 x 352 x 215 mm
Net weight:	10 kg
Shipping method:	Parcel service