

# KERN CT3000-3P2

Measuring cells made from stainless steel



## Measuring system

Combined Error:	0,023 %
Load cell connection:	4-Leiter
Nominal sensitivity:	3
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	3 t
Y value:	10000

## Environmental conditions

Maximum operating temperature:	65 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-35 °C
Minimum operating temperature:	-10 °C

## Category

Brand:	Sauter
--------	--------

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	285 x 195 x 95 mm
Gross weight:	2 g
Net weight:	950 g
Shipping method:	Parcel service

## Construction

Cable length:	6 m
Dimensions (WxDxH):	171,5 x 40 x 38,1 mm

## Piktogramme

STANDARD

