

KERN CT500-3Q1

Scherstab-Messzellen aus rostfreiem Stahl mit IP69-Schutz



Measuring system

Combined Error:	0,017 %
Load cell connection:	6-Leiter
Nominal sensitivity:	2
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	500 kg
Y value:	10000

Environmental conditions

Maximum operating temperature:	70 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-30 °C
Minimum operating temperature:	-10 °C

Category

Brand:	Sauter
--------	--------

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	250 x 155 x 60 mm
Gross weight:	1,095 kg
Net weight:	1 kg
Shipping method:	Parcel service

Construction

Cable length:	5 m
Dimensions (WxDxH):	130 x 31,5 x 31,5 mm

Piktogramme

STANDARD

