


Data Sheet

20pcs 2:1 Thin Wall Color Heat Shrinking Tube Set Typ. T1904CA041



Material: Polyolefin
 Shrinking ratio: 2:1
 Tensile strength: $\geq 10.3\text{Mpa}$
 Withstand voltage: 2kv/60s
 Volume resistance: $\geq 10^{14}\ \Omega/\text{cm}$
 Flammability: VW-1
 Operating Temperature: $-55 \sim 110^\circ\text{C}$
 Minimum shrink temperature: 70°C
 Full recovery temperature: 110°C



Nominal size (mm)	Before shrink(ømm)		After shrink(ømm)		Length
	Inner dia.	W.T	I.D. (max.)	W.T (min.)	
ø5.0	5.5±0.3	0.25±0.05	2.50	0.56	500 mm
Contents					
Black x4	Red x4	Yellow x4	Green x4	Blue x4	