

## Data Sheet

# HDMI terminal connector modular

Typ. T1904C104



Screwdriver Included



Dimension: 47 x 23 17 mm

- 1 TMDS Data2 +
- 2 TMDS Data2 Shield
- 3 TMDS Data2 -
- 4 TMDS Data1 +
- 5 TMDS Data1 Shield
- 6 TMDS Data1 -
- 7 TMDS Data0 +
- 8 TMDS Data0 Shield
- 9 TMDS Data0 -
- 10 TMDS Clock +
- 11 TMDS Clock Shield
- 12 TMDS Clock -
- 13 CEC
- 14 N/C (Reserved)
- 15 SCL
- 16 SDA
- 17 DDC/CEC Ground
- 18 +5V Power
- 19 Hot Plug Detect

Material:

Housing: PP

Contact: Copper Alloy

Contact plated: gold

Technical:

Contact current rating: 0.5A min.

Voltage rating: 40V AC(rms)

Insulation resistance: 100M $\Omega$  min.

Contact resistance: 30m  $\Omega$  max.

Operation temperature: -20 ~85°C