


Data Sheet

Heat Shrink Insulated Crimp Butt Connector Set



Adhesive Lined Heat shrink Sleeve
 Shrinking Ratio: 3:1
 Insulation Material - HDPE
 Terminal Material - Copper
 Terminal Thickness - 1.0mm
 Temperature rating - 150°C max.
 Rating voltage: 600 V/AC max.
 Rating current:
 Red - 9 Amp. max.
 Blue - 15 Amp. max.
 Yellow - 20 Amp. max.



Type	Dimension(mm)			Wire range	Color	Contents
	ød	øD	L			
T1904C068	1.7	4.0	33.3	0.5-1.5 mm ² 22-16 AWG	Red	10pcs
T1904C069	2.3	5.5	34.3	1.5-2.5 mm ² 16-14 AWG	Blue	10pcs
T1904C070	3.4	6.4	41.0	4.0-6.0 mm ² 12-10 AWG	Yellow	10pcs