


| Daten | | INDEX | | Benennung/Designation | | | |
|------------|-------------|-------|--|---|----------|----------------|---|
| Voltage | 12VDC | | | ITS-VEL-1510B-12VDC | | | |
| Watts | 1,8W (100%) | | | Projektnummer | | | |
| Current | 0,15A | | |  | Drawn | JKR 09.05.2019 | 1 |
| Resistance | 80Ω±10% | | | | Checked | BM 09.05.2019 | / |
| | | | | | Approved | | 1 |