

# KERN CPB6K0.1N

Profimodell auch mit Eichzulassung [M], Zählauflösung bis zu 60.000 Punkte



## Measuring system

Adjustment options:	External calibration
Linearity:	400 mg
Readout [d]:	100 mg
Recommended adjusting weight:	5 kg (F2); 1 kg (F2)
Reproducibility:	200 mg
Resolution:	60000
Stabilisation time:	2 s
Tare range:	6 kg
Warm up time:	2 h
Weighing range [Max]:	6 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	2 cm
-----------------------	------

## Counting

Counting resolution:	60000
Minimum piece weight at piece counting (Laboratory):	100 mg
Minimum piece weight at piece counting (Normal):	1 g
Reference weight:	yes

## Functions

Counting function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	90 h
Operating time (Backlight on):	50 h
Rechargeable battery:	Rchrg. battery optional - intern

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	445 x 375 x 210 mm
Gross weight:	4,400 kg
Net weight:	3,200 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	315 x 350 x 100 mm
Dimensions of display device (WxDxH):	315 x 350 x 125 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	320 x 350 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	295 x 225 mm