

KERN CPB 15K0.2N

Profimodell auch mit Eichzulassung [M], Zählauflösung bis zu 60.000 Punkte



Measuring system

Adjustment options:	External calibration
Linearity:	800 mg
Readout [d]:	200 mg
Recommended adjusting weight:	10 kg (F2); 5 kg (F2)
Reproducibility:	400 mg
Resolution:	75000
Stabilisation time:	2 s
Tare range:	15 kg
Warm up time:	2 h
Weighing range [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	2 cm
-----------------------	------

Counting

Counting resolution:	60000
Minimum piece weight at piece counting (Laboratory):	250 mg
Minimum piece weight at piece counting (Normal):	2,500 g
Reference weight:	yes

Functions

Counting function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	90 h
Operating time (Backlight on):	50 h
Rechargeable battery:	Rchrg. battery optional - intern

Service

DAkKS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	370 x 450 x 220 mm
Gross weight:	4,366 kg
Net weight:	3,300 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	315 x 350 x 100 mm
Dimensions of display device (WxDxH):	315 x 350 x 125 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	315 x 350 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	295 x 225 mm