

KERN EOB60K20



Die Klassiker unter den Paket- und Veterinärwaagen â auch mit XL-Plattform und großen Wägebereichen



Measuring system

| | |
|-------------------------------|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 40 g |
| Readout [d]: | 20 g |
| Recommended adjusting weight: | 40 kg (M2) |
| Reproducibility: | 20 g |
| Resolution: | 3000 |
| Stabilisation time: | 3 s |
| Tare range: | 60 kg |
| Warm up time: | 10 min |
| Weighing range [Max]: | 60 kg |
| Weighing system: | Strain gauge |
| Weighing units: | kg lb |

Display

| | |
|-----------------------|----------|
| Display digit height: | 2,500 cm |
|-----------------------|----------|

Functions

| | |
|--|-----|
| Data hold function: | yes |
| Vibration-free weighing (Animal weighing program): | yes |

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 35 °C |
| Minimum ambient temperature: | 10 °C |

Power supply

| | |
|----------------|------------------------|
| Input voltage: | 220 V - 240 V AC 50 Hz |
| n/a: | CH EURO |

| | |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

Power supply

| | |
|-----------------|------|
| Operating time: | 60 h |
|-----------------|------|

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

| | |
|----------------|----------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Platform scale |

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 475 x 415 x 130 mm |
| Gross weight: | 5,640 kg |
| Net weight: | 4,800 kg |
| Shipping method: | Parcel service |

Construction

| | |
|---------------------------------------|-------------------|
| Cable length of display device: | 2,200 m |
| Casing material: | plastic |
| Dimensions of display device (WxDxH): | 210 x 110 x 45 mm |
| Dimensions of weighing plate (WxDxH): | 315 x 305 x 55 mm |
| Material weighing plate: | stainless steel |
| Weighing surface (WxD): | 310 x 300 mm |