


# JT-DPH5005

Programmable laboratory power supply



The JT-DPH5005 power supply fulfills any requirement with its design and functionality.

Voltages can be changed both up and down.

## MAIN FEATURES

Display type	LCD
Input voltage	6 - 50 V (DC)
Output voltage	0 - 50 V
Output current	0 - 5 A
Output power	0 - 250 W
Voltage resolution	0,01 V
Current resolution	0,001 A
Size display module	43 x 79 x 38 mm
Size power module	93 x 35 x 72 mm
Display size	1,5 inch
Items delivered	Display - and power-module, 2 connection wires

## FURTHER SPECIFICATIONS

Special features	programmable, slim
Optional Equipment	BT- and USB module
Ripple	100mVpp

## FURTHER DETAILS

Article No.	JT-DPH5005
EAN:	4250236818719
Customs Tariff No.	85044030