

Supplier	Article description	Art. No. / EAN	Warranty	
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Garden pump GP 4000 INOX	31371	24 Months	
		4011458313716		
	Master Box Information			
	Master Box dimensions in cm			weight (kg) gross
	Width	Depth	Height	
-	-	-	-	
Article Information				
Color Box dimensions in cm			weight (kg) net / gross	
Width	Depth	Height		
39.0	19.5	27.0	6,6 / 7,8	

Garden pump GP 4000 INOX	quantity / pallet:	
	quantity / truck:	

Description:

Robust, self-priming jet pump with stainless steel pump housing, on-off switch and ergonomic handle. For pumping clear water. For filling and emptying water tanks, etc. Due to the high efficiency, this device is also well suited for the operation of sprinklers.

Technical Data:

Nominal performance: 800 Watt
 Delivery height max.: 42 m / 4.2 bar
 Flow rate max.: 66 l/min / 4,000 l/h
 Suction height max.: 9 m
 Pump housing: stainless steel
 Pressure port: 30.93 mm (1" female)
 Suction port: 30.93 mm (1" female)
 Temp. max. liquid: 35 °C
 Power cord: 1.5 m / H07RN-F
 Number of sprinklers max.: 3



Approval marks:

CE