

Supplier	Article description	Art. No. / GTIN	Warranty	
<b>T.I.P.</b> <b>Technische Industrie Produkte GmbH</b> <b>Siemensstr. 17</b> <b>74915 Waibstadt</b>  <b>Tel.: 07263-9125-0</b> <b>Fax: 07263-9125-25</b>  <b>www.tip-pumpen.de</b>	<b>Drainage submersible pump</b> <b>I-Compac 7500</b>	<b>30190</b>	<b>24</b> <b>Months</b>	
		4011458301904		
	<b>Master Box Information</b>			
	<b>Master Box dimensions in cm</b>			<b>weight (kg) gross</b>
	<b>Width</b>	<b>Depth</b>	<b>Height</b>	
46.0	38.3	38.0	18.6	4
<b>Article Information</b>				
<b>Color Box dimensions in cm</b>			<b>weight (kg) net / gross</b>	
<b>Width</b>	<b>Depth</b>	<b>Height</b>		<b>Qty.</b>
22.0	18.0	36.0	4.2 / 4.5	1

**Drainage submersible pump**  
**I-Compac 7500**

quantity / pallet:

quantity / truck:

**Description:**

Specially designed for dirty water drainage submersible pump with vertical pump outlet and integrated float switch. For use in drainage shafts, this pump can be switched from automatic to manual operation. Can also be used for polluted water to 16 mm grain size.

**Technical Data:**

Nominal performance: 400 Watt  
Mains voltage / frequency: 230 - 240 V~ / 50 Hz  
Delivery height / pressure max.: 5 m / 0.5 bar  
Flow rate max.: 7,500 l/h / 125 l(min)  
Pump housing: Plastic  
Suction level min.: 25 mm  
Grain size max.: 16 mm  
Submersion depth max.: 5 m  
Power cord: 10 m / 05RN8-F  
Max. fluid temp.: 35° C  
Pressure port: 47.8 mm (1½" male)

**Scope of delivery:**

- MultiDimension fitting: 45.48 mm (1½", female)  
- 33.25 mm (1", female) - Ø 33 mm - Ø 25 mm

**Approval marks:**

