

Supplier	Article description			Art. No. / GTIN	Warranty
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Garden pump GPP 2100 M			30183	24 Months
	Master Box Information				
	Master Box dimensions in cm			weight (kg) gross	pack. Unit (pcs.)
	Width	Depth	Height		
33.5	29.5	38.0	23.5	4	
Article Information					
Color Box dimensions in cm			weight (kg) net / gross	Qty.	
Width	Depth	Height			
28.0	18.0	20.5	6.6 / 7.1	1	

Garden pump GPP 2100 M	quantity / pallet:	144
	quantity / truck:	4,752

Description:

Robust peripheral pump with cast iron pump housing, brass impeller and on-and-off switch. Pump is not self-priming. Stainless steel inlay to prevent blocking of motor by rust.

Maintenance-free capacitor motor with thermal overload protection.

Technical Data:

Motor:	550 Watt
Delivery height / pressure max.:	35 m / 3.5 bar
Flow rate max.:	35 l/min / 2,100 l/h
Pump housing:	Cast iron
Impeller:	Brass
Power cord:	1.5 m / H07RN-F
Pressure connection:	30.93 mm (1" female)
Suction connection:	30.93 mm (1" female)
Fluid temp. max.:	40 °C



Approval marks:

