

Supplier	Article description	Art. No. / EAN	Warranty	
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Booster set HWW 3000 INOX	31143	24 Months	
		4011458311439		
	Master Box Information			
	Master Box dimensions in cm			weight (kg) gross
	Width	Depth	Height	
-	-	-	-	pack. Unit (pcs.)
-	-	-	-	-
Article Information				
Color Box dimensions in cm			weight (kg) net / gross	Qty.
Width	Depth	Height		
48.5	29	50	9.9 / 11.3	1

Booster set HWW 3000 INOX	quantity / pallet:	24
	quantity / truck:	792

Description:

Compact size, flexible and self-priming booster set.

Pump housing and pressure tank are made of high-grade steel and with food-proof diaphragm.

For discharging water at a constant pressure, domestic water supply, pressure boosting, watering and irrigation.

Technical Data:

Nominal performance: 550 Watt
 Delivery height / pressure max.: 42 m / 4.2 bar
 Flow rate max.: 49 l/min / 2,950 l/h
 Suction height max.: 9 m
 Pump housing: Stainless steel
 Pressure tank / volume: Stainless steel / 18 l
 Pressure port: 30.93 mm (1" female)
 Suction port: 30.93 mm (1" female)
 Fluid temp. max.: 35 °C
 Power cord: 1.5 m / H05RN-F
 Sprinklers max.: 1 pc.



Approval marks:





www.tuv.com
ID 1000000000