

Product Information

without engagement until placement of order

Supplier	Article description	Art. No. / EAN	Warranty	
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Garden Pump Garten-Jet 1000 Plus	30186	24 Months	
		4011458301867		
	Master Box Information			
	Master Box dimensions in cm			weight (kg) gross
	Width	Depth	Height	
-	-	-	-	
Article Information				
Color Box dimensions in cm			weight (kg) net / gross	
Width	Depth	Height		
39.2	19.3	26.3	8,9 / 10,4	

Garden Pump
Garten-Jet 1000 Plus

quantity / pallet:

quantity / truck:

Description:

Robust, self-priming jet pump with iron cast pump housing and comfortable handle for easy use. Garden pump to deliver clear water and to transfer with pressure. Maintenance-free capacitor motor with thermal overload protection and On - / Off switch. Fields of application: Lawn sprinklers, irrigation of plots /beds, filling or draining storage tanks or basins, rising terrace and path.

Technical Data:

Motor:	800 Watt
Delivery height / pressure max.:	46 m / 4,6 bar
Flow rate max.:	58 l/min / 3,500 l/h
Suction max.:	9 m
Pump housing:	cast iron
Pump inlet:	30,93 mm (1" female)
Pump output:	30,93 mm (1" female)
Temp . Ma . Liquid:	35 °C
Power cord:	1,5 m / H07RN-F
Number of sprinklers max.:	3



Approval marks:

