

# TEX-FLEX

## 10



### SPECIFICATIONS

- Weight: 405g
- Dimensions: 82mm x 133 x 25mm (folded)  
254mm x 133mm x 9mm (unfolded)
- Input: 5V at 2 amps
- Output: 5V at 2 amps, 8.4 DC, 12V DC
- Capacity: 10,500 mAh lithium-polymer 38.85Wh
- Cable: 1m extension cable
- Material: Waterproof leather
- Operating temp: -20°C to + 20°C
- Waterproof protection: Battery IP67, Controller IP65
- Warranty: 2 years

### FEATURES

- Lightweight, compact (foldable) and efficient
- Waterproof leather – soft feel, durable and flexible
- Magnetic – attaches to most metal surfaces
- Functions in extreme temperatures
- Compatible with USB chargeable devices
- Auto on/off sensing technology
- LED screen shows output with single button control
- Stack multiple Tex-Flex 10's via an external connector for increased capacity up to 42,000 mAh
- Battery totally waterproof IP67 rated in general use, can be submerged up to 1 metre. Controller IP65 rated - dust and splashproof

