







# **Model Number**


#### **AIR17-S Master**

Replacement/extension sensor module


### **Features**

- Sensor module for configurable TopScan-S
- Master module
- Category 2, tested and certified to DIN 18650/EN 16005
- Safe function even on difficult floors
- Easy adjustment of transmitter for hinge side/ opposite hinge side

# **Dimensions**



### **Electrical connection**



Explanation:

Relay: Relay is inactive during detection Relay is active in free detection field

Test input: Test input is inactive at: Test input is active at:

U\_low = -3 V ... +5 V DC U\_high = +11 V ... +30 V DC

### Mechanical specifications Mounting height

Ambient temperature

max. 2500 mm

Safety fuse ≤ 1 A (slow-blow) according to IEC 60127-2 Sheet 1 Note


-10 ... 50 °C (14 ... 122 °F)

Recommendation: after a short circuit, check that the device is functioning correctly.

#### Approvals and certificates

CCC approval / marking not required for products rated  $\leq$ 36 V CCC approval

## Design of the device



**PEPPERL+FUCHS** Singapore: +65 6779 9091