











Model Number


RL29-55/25/73c/136

Retroreflective sensor with 4-pin, M12 x 1 plastic connector


Features

- Highly visible LED
- Powerful push-pull output
- Optimal price/power ratio
- Protection class II

Dimensions



Electrical connection



- O = Light on
- = Dark on

Pinout

Wire colors in accordance with EN 60947-5-2



1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)



Technical data

Reference target

Light source

Light type

General specifications
Effective detection range
Threshold detection range

0.1 ... 7 m 10 m H85 reflector

LED, 660 nm

modulated visible red light

Polarization filter

Diameter of the light spot approx. 150 mm at a distance of 7 m Emitter: 1.2 °, Receiver: 2 ° Anale of divergence

Ambient light limit 80000 Lux

Functional safety related parameters 1982.2 a MTTF_d Mission Time (T_M) Diagnostic Coverage (DC) 0%

Indicators/operating means

Function indicator LED yellow, light with free light beam, flashes when falling short of the stability control

Electrical specifications

No-load supply current

10 ... 30 V DC , class 2 Operating voltage Ripple 10 % ≤ 30 mA

Output

Switching type

Signal output 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected

Switching voltage max. 30 V DC Switching current max. 100 mA Switching frequency 500 Hz Response time 1 ms

Ambient conditions

Ambient temperature -25 ... 60 °C (-13 ... 140 °F) Storage temperature -40 ... 75 °C (-40 ... 167 °F)

Mechanical specifications

Housing width 25.8 mm Housing height 88 mm Housing depth 54.3 mm Degree of protection IP65

Plastic connector M12 x 1, 4-pin Connection

Material

Plastic ABS Housing Optical face plastic Mass 70 g

Compliance with standards and directi-

ves


Directive conformity

EMC Directive 2004/108/EC EN 60947-5-2:2007

Approvals and certificates

UL approval cULus Listed, Class 2 Power Source, Type 1 enclosure CCC approval CCC approval / marking not required for products rated ≤36 V CE, cULus Listed 57M3 (Only in association with UL Class 2 Approvals power supply; Type 1 enclosure)

Curves/Diagrams



Accessories

OMH-05

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

OMH-21

Mounting bracket

OMH-22

Mounting bracket

OMH-MLV11-K

dove tail mounting clamp

OMH-RLK29-HW

Mounting bracket for rear wall mounting

OMH-RL28-C

Weld slag cover model

V1-G-2M-PUR

Female cordset, M12, 4-pin, PUR cable

V1-W-2M-PUR

Female cordset, M12, 4-pin, PUR cable

Suitable reflectors and cable sockets can be found in the Internet