




Pressure pipe flange, 1/2 inch, +pressure gauge connection

Part no. M-MCS
Catalog No. 071913
Alternate Catalog No. M-MCS

Delivery program

Product range		Accessories
Basic function		Pressure pipe flange with pressure gauge connection
		Article no. when ordered separately
For use with		MCS



Notes

Manometer connection R ¼",
Pressure pipe flange always R ½" also with MCS

Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-25
Operating ambient temperature max.	°C	70

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Accessories for low-voltage switch technology (EC002498)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Component for low-voltage switch technology (accessories) (ecl@ss10.0.1-27-37-13-92 [AKN570013])		
Type of accessory		Connection technique

Approvals

Product Standards		CSA-CC22.2 No. 14
CSA File No.		12528
CSA Class No.		3211-06
North America Certification		CSA certified

