




Wall fixing bracket, for pressure switch

Part no. W-MCS
Catalog No. 050665
Alternate Catalog No. MCSX-W
EL-Nummer (Norway) 4356154

Delivery program

Product range		Accessories
Basic function		Wall fixing bracket
		Article no. when ordered separately
For use with		MCS, MCSN



Notes

Wall mounting bracket can be rotated to right or left by 90°

Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-25
Operating ambient temperature max.	°C	70

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Accessories for low-voltage switch technology (EC002498)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Component for low-voltage switch technology (accessories) (ecl@ss10.0.1-27-37-13-92 [AKN570013])		
Type of accessory		Other

Approvals

Product Standards		CSA-CC22.2 No. 14
CSA File No.		12528
CSA Class No.		3211-06
North America Certification		CSA certified

Dimensions

