



Two way switch 22 CO, 16A, 230 V, 20kA

Part no. Z-S/2WM

Catalog No. 248346

EL-Nummer (Norway) 0004355527

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I _n	A	20

Technical data ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Main switch for distribution board (EC001545)			
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Main switch for distribution board (ecl@ss10.0.1-27-14-23-01 [AFZ813014])			
Switching function			Two-way switch
Number of contacts as normally open contact			0
Number of contacts as normally closed contact			0
Number of contacts as change-over contact			2
Number of poles			0
Rated current		A	16
Rated voltage		V	230
Min. rated voltage		V	0
Rated switching capacity		kA	20
Short-circuit breaking capacity (I _{cw})		kA	10
Voltage type			AC
Forced segregation (according to DIN VDE 0113)			No
With signal lamp			No
Colour calotte			Other
Lamp type			Other
Lamp socket			Other
Max. lamp power		W	0
Width in number of modular spacings			2
Built-in depth		mm	80
Degree of protection (IP)			IP40