



Switch with LED, 230AC/DC, 1N/O, 16A, orange, 1HP

Part no. Z-SWL230/S  
 Catalog No. 292300

### Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	$I_n$	A	16
Heat dissipation per pole, current-dependent	$P_{vid}$	W	2
Equipment heat dissipation, current-dependent	$P_{vid}$	W	2

### Technical data ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Main switch for distribution board (EC001545)			
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Main switch for distribution board (ec1@ss10.0.1-27-14-23-01 [AFZ813014])			
Switching function			Off switch
Number of contacts as normally open contact			1
Number of contacts as normally closed contact			0
Number of contacts as change-over contact			0
Number of poles			0
Rated current		A	16
Rated voltage		V	250
Min. rated voltage		V	0
Rated switching capacity		kA	0
Short-circuit breaking capacity (I <sub>cw</sub> )		kA	0
Voltage type			AC
Forced segregation (according to DIN VDE 0113)			No
With signal lamp			Yes
Colour calotte			Other
Lamp type			LED
Lamp socket			Other
Max. lamp power		W	0
Width in number of modular spacings			1
Built-in depth		mm	80
Degree of protection (IP)			IP40