



REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
①		增加UL刻字	CSX	08/08/07
②		品名、料号增加环保标示“(H)”	LJH	12/10/07
③		增加VDE刻字	Zengy	09/05/08
④		增加限位结构	CW	05/18/09
⑤	15-0234	弹片使用国产不锈钢, 更新料号	WWF	06/19/15

NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.RATED VOLTAGE/CURRENT: UL 600V/15A
VDE 800V/24A
- 3.OPERATION TEMPERATURES: -40℃~+105℃
- 4.RATED IMPULSE VOLTAGE: 8KV
- 5.INSULATION RESISTANCE: 5000MΩ/DC1000V
- 6.WIRE RANGE: 28~14AWG, 2.5MM²
- 7.UNDIMENSIONED TOLERANCES:

Pitch range in mm		Nominal dimension range in mm					
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0 0.05/10



ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTES
3	WS 2.5-Current Carrier	6027B00010(H)	1	Copper	Sn plated
2	DG242-5.0-Shrapnel	X000006250(H)	2	Stainless steel	
1	WS 2.5-Housing	6027A0Y01A(H)	1	PA66	UL94V-0

DETACHED LISTS		MATERIAL:	宁波高正电子有限公司	
TOLERANCES EXCEPT AS NOTED		FINISH:	DEGSON® DEGSON ELECTRONICS CO., LTD	
.X ±	.X" ±	PART NO.:	NAME: WS2.5-01P-1Y-00A(H)	
.XX ±	.XX" ±	APPD: <i>Aaron 6/26/05</i>	TITLE: ASSEMBLY DRAWING	
.XXX ±	.XXX" ±	CHKD: <i>penry/bk-15</i>	DRAWING NO.: WS2.5-E01	
ANGLES ± 1°		DRFT: LYK 12/01/06	DO NOT SCALE DRAWING	SCALE N/A
THIRD ANGLE PROJECTION			SHEET	1/1