


标注公差/General tolerances(mm)													D
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	
~	~	~	~	~	~	~	~	~	~	~	~	~	>500
3	6	10	18	30	50	80	120	180	250	315	400	500	
±0.12 ±0.18 ±0.22 ±0.26 ±0.31 ±0.37 ±0.57 ±0.80 ±0.93 ±1.05 ±1.15 ±1.60 ±2.20 ±2.50													±Z



REV	ECN	DESCRIPTION	DRAFT	DATE	SIZE: A4	TYPE: CUSTOMER DRAWING	SCALE: 2:1	SHEET 1/1
-----	-----	-------------	-------	------	----------	------------------------	------------	-----------

ITEM	NAME OF PART	MATERIAL	NOTES
1	Bridge		
间距/Pitch(mm)/线数范围/Poles			
使用温度范围/Operating temperature(°C)			
符合RoHS环保要求/Conform to RoHS			

MATERIAL:	/	SURFACE:	/
-----------	---	----------	---

MAT NO.:	/	NINGBO DEGSON ELECTRICAL CO., LTD	
STATUS:	/		

NAME:	EB10-12-1Y-00A(H)
APPD:	LI GL 2020.06.10
CHKD:	Moo J 2020.06.10

DRAFT:	Chen K 2020.06.03	DRAWING NO.:	EB10-12-C01	REV	T0
--------	-------------------	--------------	-------------	-----	----