

Data Sheet

4 mm Banana Plug assortment

Typ. T1906C150



1x Screwdriver

Color	DiaØ	Length (mm)±0.5	Voltage rating (max.)	Current rating (max.)	Contents Plug
Blue	4 mm	55.8	60V/DC	19 A	2pcs
Yellow	4 mm	55.8	60V/DC	19 A	2pcs
Green	4 mm	55.8	60V/DC	19 A	2pcs
Black	4 mm	55.8	60V/DC	19 A	2pcs
Red	4 mm	55.8	60V/DC	19 A	2pcs