

Data Sheet

4mm Binding post banana socket Set

Typ. T1906C141/T1906C142/T1906C143/T1906C144/T1906C145/T1906C146/T1906C147



Type	DiaØ	Length (mm)±0.5	Voltage rating (max.)	Current rating (max.)	Color	Contents
T1906C141	4 mm	21.3	60 V/DC	24 A	Blue / Yellow / Green / Black / Red / Silver	12pcs (2pcs each)
T1906C142	4 mm	21.3	60 V/DC	24 A	Blue	10pcs
T1906C143	4 mm	21.3	60 V/DC	24 A	Yellow	10pcs
T1906C144	4 mm	21.3	60 V/DC	24 A	Green	10pcs
T1906C145	4 mm	21.3	60 V/DC	24 A	Black	10pcs
T1906C146	4 mm	21.3	60 V/DC	24 A	Red	10pcs
T1906C147	4 mm	21.3	60 V/DC	24 A	Silver	10pcs