























Wire connector with grease filling Set



Feature:

- Self-Stripping
- Moisture resistant
- Waterproof

Type	Product	Poles	Wire dia.	Conductor dia.	Insulation material	Color	Contents
1905C129		3 	3,8 mm (max.)	0,8 ~1,4 mm	PA	Blue	15pcs
1905C130		2 	1,52 mm (max.)	0,4 ~0,7 mm	PC	Yellow	15pcs
1905C131		2 	2,08 mm (max.)	0,4 ~0,9 mm	PP	Orange	15pcs
1905C132		3 	2,08 mm (max.)	0,4 ~0,9 mm	PP	Red	15pcs
1905C133		4 	3,18 mm (max.)	0,9 ~1,3 mm	PC	Green	10pcs
1905C134		4 	3,18 mm (max.)	0,5 ~0,9 mm	PC	Red	10pcs
1905C135		2 	1,67 mm (max.)	0,4 ~0,9 mm	PC	Green	15pcs
1905C136		4 	4,4 mm (max.)	0,9 ~1,3 mm	PC	Black	10pcs
1905C137		4 	1,4mm (max.)	0,4 ~0,7 mm	PC	Transparent	10pcs
1905C138		4 	1,4 mm (max.)	0,4 ~0,7 mm	PC	Blue	10pcs
1905C139		4 	1,4 mm (max.)	0,4 ~0,7 mm	PC	Green	10pcs