





## Clamp-type test probe

### KLEPS 2900



Product	KLEPS 2900
description	Safety clamp-type test probe with rigid hook to ensure secure clamping of eyes, pins, wires and boards. 4 mm brass socket connection. Connects with safety measuring leads.
operating instruction	BA458
article-no. / *colour	9723091xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  00 black         </div> <div style="text-align: center;">  01 red         </div> </div>
drawing	
technical data	
connection	unsprung socket 4 mm
rated voltage <sup>(1)</sup>	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT III
rated current <sup>(1)</sup> (consider derating curve)	20 A
material plug	brass, nickel plated
material socket	brass
housing material	PBT
temperature range acc. To IEC61010 <sup>(2)</sup>	-25 °C to +70 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	HB

4 mm safety system

clamp type	contact hook
clamping range	5,5 mm
standard	IEC 61010

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

stand: 10.01.2019