

Set

PMS 250



4 mm sliding sleeve system

Product	PMS 250
description	<p>Sliding sleeve test equipment set for 4 mm system.</p> <ul style="list-style-type: none"> - Kleps 250 Contact-protected clamp-type test probe with rotating grip jaws and flexible shaft to clamp wires and pins up to ø 4mm. - PRUEF 2 S Contact-protected test probe with slender stainless steel tip for penetration of insulation and oxide layers. - AK 2 B Safety alligator clip for secure contacting of fine wires, clamping range up to 9,5 mm bolt diameter. - MLB 100/1 V Contact-protected measuring lead with 4 mm plugs and 4 mm sockets for tower construction on both sides. Spring-loaded insulated sleeve is only released by pressure on the side-mounted locking spring. (length:100 cm) <p>Please find further technical details on individual product data sheets.</p>
Articlenummer	932827001
technical data	
scope of delivery	<p>1 x clamp-type test probe KLEPS 250 black (973 528-100) 1 x clamp type test probe KLEPS 250 red (973 528-100) 1 x test probe PRUEF 2 S black (973 659-100) 1 x test probe PRUEF 2 S red (973 659-100) 1 x alligator clip AK 2 B black (932 435-100) 1 x alligator clip AK 2 B red (932 435-100) 1 x measuring lead MLB 100/1 V black (973 646-100) 1 x measuring lead MLB 100/1 V red (973 646-100)</p>

stand: 04.07.2018