





Datenblatt



RECOMMENDED P.C.B LAYOUT



MATERIAL

HOUSING : NYLON 6T,UL94V-0

CONTACT : COPPER ALLOYS

PLATED : GOLD-FLASH

COLOR : BLACK

SPECIFICATION

CURRENT: 1A

OPERATING TEMPERATURE: -55°C TO $+105^{\circ}\text{C}$

CONTACT RESISTANCE : 20 MILLIOHMS MAX

INSULATION RESISTANCE : 500 MEGAOHMS MIN

DIELECTRIC STRENGTH : 200 VAC MIN

A: 8.00 mm B: 3.00 mm C: 3.00 mm